

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1303050210](#)
Status: **Active**
Overview: [Brad Micro-Change \(M12\) Connectors](#)
Description: M12 Wide Area LED Machine Light Kit, 170.00mm Width, 420.00mm Length, 25W

Documents:
[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Portable Lighting
Series [130305](#)
Connector End Micro-Change® (M12)
IP Rating IP67
NEMA Configuration N/A
Outlet None
Overview [Brad Micro-Change \(M12\) Connectors](#)
Product Name M12 LED Machine Light
Type Ind Automation Machine Lights
UPC 78172558209

Physical
Cord Length - Primary 5.0m (16.40')
Cord Length - Secondary N/A
Depth 170.00mm (6.69")
Duty Industrial
Guard Included No
Guard Type N/A
Height 40.00mm (1.570")
Length 420.00mm (16.53")
Material - Guard N/A
Mounting Style Screw-Bracket
Packaging Type Carton
Socket Construction N/A

Electrical
Bulb Type LED - 5800K
Cord Type - Primary 22/5 WSOR
Cord Type - Secondary 22/5 WSOR
Lamp Type LED
Lamp Wattage - Maximum 25W
Lumens 1880
On/Off Switch No
Voltage (Fixture) - Maximum 24V DC

Material Info
Engineering Number M12MXISLUMA-25W



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[130305](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

1303050210