High Temperature 150°C, Ultra-Stable X8R Dielectric, 10 – 100 VDC (Commercial & Automotive Grade)




Surface Mount Multilayer Ceramic Chip Capacitors (SMD MLCCs)

Overview

KEMET's Ultra-Stable X8R dielectric features a 150°C maximum operating temperature, offering the latest in high temperature dielectric technology and reliability for extreme temperature applications. It offers the same temperature capability as conventional X8R, but without the capacitance loss due to applied DC voltage. Ultra-Stable X8R exhibits no change in capacitance with respect to voltage and boasts a minimal change in capacitance with reference to ambient temperature. It is a suitable replacement for higher capacitance and larger footprint devices that fail to offer capacitance stability. Capacitance change with respect to temperature is limited to ±15% from -55°C to +150°C.

Driven by the demand for a more robust and reliable component, Ultra-Stable X8R dielectric capacitors were developed for critical applications where reliability and capacitance stability at higher operating temperatures are a concern. These capacitors are widely used in automotive circuits as well as general high temperature applications.

In addition to commercial grade, automotive grade devices are available and meet the demanding Automotive Electronics Council's AEC-Q200 qualification requirements.



Ordering Information

С	1210	С	184	K	3	Н	A	С	AUT0
Ceramic	Case Size (L" x W")	Specification/ Series ¹	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Dielectric	Failure Rate/Design	Termination Finish ²	Packaging/ Grade (C-Spec)
	0402 0603 0805 1206 1210 1812	C = Standard	Two significant digits and number of zeros	B = ±0.10 pF C = ±0.25 pF D = ±0.5 pF F = ±1% G = ±2% J = ±5% K = ±10% M = ±20%	8 = 10 4 = 16 3 = 25 5 = 50 1 = 100	H = Ultra Stable X8R	A = N/A	C = 100% Matte Sn L = SnPb (5% Pb minimum)	See "Packaging C-Spec Ordering Options Table"

¹ Flexible termination option is available. Please see FT-CAP product bulletin C1013_X8R_FT-CAP_SMD.

² Additional termination finish options may be available. Contact KEMET for details.

² SnPb termination finish option is not available on automotive grade product.

Packaging C-Spec Ordering Options Table

Packaging Type	Packaging/Grade Ordering Code (C-Spec)
Commerc	ial Grade ¹
Bulk Bag	Not Required (Blank)
7" Reel/Unmarked	TU
13" Reel/Unmarked	7411 (EIA 0603 and smaller case sizes) 7210 (EIA 0805 and larger case sizes)
Automotiv	ve Grade ²
7" Reel	AUTO
13" Reel/Unmarked	AUTO7411 (EIA 0603 and smaller case sizes) AUTO7210 (EIA 0805 and larger case sizes)

¹ Default packaging is "Bulk Bag". An ordering code C-Spec is not required for "Bulk Bag" packaging.

Benefits

- -55°C to +150°C operating temperature range
- · Lead (Pb)-Free, RoHS and REACH compliant
- EIA 0402, 0603, 0805, 1206, 1210, and 1812 case sizes
- DC voltage ratings of 10 V, 16 V, 25 V, 50 V and 100 V
- Capacitance offerings ranging from 0.5 pF to 0.22 μF
- Available capacitance tolerances of ±0.10 pF, ±0.25 pF. ±0.5 pF, ±1%, ±2%, ±5%, ±10%, and ±20%
- Extremely low ESR and ESL
- High thermal stability
- High ripple current capability

- No capacitance change with respect to applied rated DC
- Non-polar device, minimizing installation concerns
- Offered in both commercial and automotive grades
- 100% pure matte tin-plated termination finish that allowing for excellent solderability.
- SnPb plated termination finish option available upon request (5% Pb minimum)

Applications

Typical applications include decoupling, bypass and filtering in extreme environments such as down-hole oil exploration, under-hood automotive, military and aerospace.



¹ The terms "Marked" and "Unmarked" pertain to laser marking option of capacitors. All packaging options labeled as "Unmarked" will contain capacitors that have not been laser marked.

² Reeling tape options (Paper or Plastic) are dependent on capacitor case size (L" x W") and thickness dimension. See "Chip Thickness/Tape & Reel Packaging Quantities" and "Tape & Reel Packaging Information".

² For additional Information regarding "AUTO" C-Spec options, see "Automotive C-Spec Information".

² All Automotive packaging C-Specs listed exclude the option to laser mark components. Please contact KEMET if you require a laser marked option. For more information see "Capacitor Marking".

High Temperature 150°C, Ultra-Stable X8R Dielectric, 10 - 100 VDC (Commercial & Automotive Grade)

Surface Mount Multilayer Ceramic Chip Capacitors (SMD MLCCs)

Automotive C-Spec Information

KEMET automotive grade products meet or exceed the requirements outlined by the Automotive Electronics Council. Details regarding test methods and conditions are referenced in document AEC-Q200, Stress Test Qualification for Passive Components. These products are supported by a Product Change Notification (PCN) and Production Part Approval Process warrant (PPAP).

Automotive products offered through our distribution channel have been assigned an inclusive ordering code C-Spec, "AUTO." This C-Spec was developed in order to better serve small and medium-sized companies that prefer an automotive grade component without the requirement to submit a customer Source Controlled Drawing (SCD) or specification for review by a KEMET engineering specialist. This C-Spec is therefore not intended for use by KEMET OEM automotive customers and are not granted the same "privileges" as other automotive C-Specs. Customer PCN approval and PPAP request levels are limited (see details below.)

Product Change Notification (PCN)

The KEMET product change notification system is used to communicate primarily the following types of changes:

- Product/process changes that affect product form, fit, function, and/or reliability
- Changes in manufacturing site
- Product obsolescence

KEMET Automotive	Customer Notifica	tion Due To:	Days Prior To
C-Spec	Process/Product change	Obsolescence*	Implementation
KEMET assigned ¹	Yes (with approval and sign off)	Yes	180 days minimum
AUT0	Yes (without approval)	Yes	90 days minimum

¹ KEMET assigned C-Specs require the submittal of a customer SCD or customer specification for review. For additional information contact KEMET.

Production Part Approval Process (PPAP)

The purpose of the Production Part Approval Process is:

- To ensure that supplier can meet the manufacturability and quality requirements for the purchased parts.
- To provide the evidence that all customer engineering design records and specification requirements are properly understood and fulfilled by the manufacturing organization.
- To demonstrate that the established manufacturing process has the potential to produce the part.


KEMET Automotive			PPAP Level		
C-Spec	1	2	3	4	5
KEMET assigned ¹	•	•	•	•	•
AUT0			0		

¹ KEMET assigned C-Specs require the submittal of a customer SCD or customer specification for review. For additional information contact KEMET.

- Part number specific PPAP available with customer information included.
- Product family PPAP only



Dimensions - Millimeters (Inches)



EIA Size Code	Metric Size Code	L Length	W Width	T Thickness	B Bandwidth	S Separation Minimum	Mounting Technique
0402	1005	1.00 (0.040) ±0.05 (0.002)	0.50 (0.020) ±0.05 (0.002)		0.30 (0.012) ±0.10 (0.004)	0.30 (0.012)	Solder Reflow Only
0603	1608	1.60 (0.063) ±0.15 (0.006)	0.80 (0.032) ±0.15 (0.006)		0.35 (0.014) ±0.15 (0.006)	0.50 (0.020)	
0805	2012	2.00 (0.079) ±0.20 (0.008)	1.25 (0.049) ±0.20 (0.008)	See Table 2 for	0.50 (0.02) ±0.25 (0.010)	0.70 (0.028)	Solder Wave or Solder Reflow
1206	3216	3.20 (0.126) ±0.20 (0.008)	1.60 (0.063) ±0.20 (0.008)	Thickness	0.50 (0.02) ±0.25 (0.010)	1.50 (0.060)	
1210	3225	3.20 (0.126) ±0.20 (0.008)	2.50 (0.098) ±0.20 (0.008)		0.50 (0.02) ±0.25 (0.010)	1.50 (0.060)	Solder Reflow
1812	4532	4.50 (0.177) ±0.30 (0.012)	3.20 (0.126) ±0.30 (0.012)		0.60 (0.024) ±0.35 (0.014)	2.30 (0.091)	Only

Qualification/Certification

Commercial grade products are subject to internal qualification. Details regarding test methods and conditions are referenced in Table 4, Performance & Reliability.

Automotive grade products meet or exceed the requirements outlined by the Automotive Electronics Council. Details regarding test methods and conditions are referenced in document AEC-Q200, Stress Test Qualification for Passive Components. For additional information regarding the Automotive Electronics Council and AEC-Q200, please visit their website at www.aecouncil.com.

Environmental Compliance

Lead (Pb)-free, RoHS, and REACH compliant without exemptions (excluding SnPb termination finish option).



Electrical Parameters/Characteristics

Item	Parameters/Characteristics
Operating Temperature Range	-55°C to +150°C
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	±15%
Aging Rate (Maximum % Capacitance Loss/Decade Hour)	0%
Dielectric Withstanding Voltage (DWV)	250% of rated voltage (5 ±1 seconds and charge/discharge not exceeding 50 mA)
Dissipation Factor (DF) Maximum Limit at 25°C	2.5%
Insulation Resistance (IR) Limit at 25°C	1,000 MΩ μF or 100 GΩ (Rated voltage applied for 120 ±5 seconds at 25°C)

To obtain IR limit, divide M Ω - μ F value by the capacitance and compare to G Ω limit. Select the lower of the two limits. Capacitance and dissipation factor (DF) measured under the following conditions:

1 MHz ± 100 kHz and 1.0 ± 0.2 V_{rms} if capacitance $\leq 1,000$ pF.

1 kHz ± 50 Hz and 1.0 ± 0.2 V_{rms} if capacitance > 1,000 pF.

Note: When measuring capacitance it is important to ensure the set voltage level is held constant. The HP4284 and Agilent E4980 have a feature known as Automatic Level Control (ALC). The ALC feature should be switched to "ON."

Post Environmental Limits

	High Temperatu	ıre Life, Biased	Humidity, Moist	ture Resistance	
Dielectric	Rated DC Voltage	Capacitance Value	Dissipation Factor (Maximum %)	Capacitance Shift	Insulation Resistance
Ultra-Stable X8R	All	All	3.0	±20%	10% of Initial Limit



Table 1 - Capacitance Range/Selection Waterfall (0402 - 1812 Case Sizes)

	Сар	Ca	ıse	Si	ze,	/Se	erie	es		C)40	2C			CI	060	3C			C)80	5C			C1	120	6C			C.	121	0C		C18	12C
Capacitance	Code		V	olta	ge (Cod	е		8	4	3	5	1	8	4	3	5	1	8	4	3	5	1	8	4	3	5	1	8	4	3	5	1	5	1
	Code	R	ated	l Vo	ltag	je (\	VDC)	10	16	25	50	100	2	16	25	50	100	10	16	25	50	100	10	16	25	50	100	10	16	25	50	100	50	100
		Ca	paci	itan	ce 1	Γole	ran	ce															Chi												
0.50 & 0.75 pF	508 & 758	В	С) [ВВ	ВВ	ВВ	ВВ		CF	CF	CF	CF	CF	DN	DN	DN	DN	hick DN	ness	וווע	iens	ions	•							
0.75 pF	758	В	C	וכ					ВВ	ВВ	ВВ	ВВ		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN						l						
1.0 - 9.1 pF* 10 pF	109 - 919* 100	В	C) F	G	J	K	М	BB BB	BB BB	BB BB	BB BB		CF CF	CF CF	CF CF	CF CF	CF CF	DN DN	DN DN	DN DN	DN DN	DN DN	EB EB	EB EB	EB EB	EB EB	EB EB	FB FB	FB FB	FB FB	FB FB	FB FB		
11 pF	110			F			K	М	BB	BB	BB	BB		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN		EB	EB	EB	EB	FB	FB	FB	FB	FB		
12 pF	120		Т	F		_	_	М	ВВ	ВВ	ВВ	ВВ		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
13 pF	130			F			K	М	ВВ	ВВ	ВВ	ВВ		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
15 pF	150			F			K	М	BB	ВВ	BB	BB		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
16 pF 18 pF	160 180			F			K	M M	BB BB	BB BB	BB BB	BB BB		CF CF	CF CF	CF CF	CF CF	CF CF	DN DN	DN DN	DN DN	DN DN	DN DN	EB EB	EB EB	EB EB	EB EB	EB EB	FB FB	FB FB	FB FB	FB FB	FB FB		
20 pF	200			F	_	_	K	М	BB	BB	BB	BB		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
22 pF	220			F			K	М	ВВ	ВВ	ВВ	BB		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
24 pF	240			F	1 -		K	М	ВВ	ВВ	ВВ	ВВ		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
27 pF	270			F			K	М	BB	BB	BB	BB		CF	CF	CF	CF	CF	DN	DN	DN	DN		EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
30 pF 33 pF	300 330			F		_	K	M M	BB BB	BB BB	BB BB	BB BB		CF CF	CF CF	CF CF	CF CF	CF CF	DN DN	DN DN	DN DN	DN DN	DN DN	EB EB	EB EB	EB EB	EB EB	EB EB	FB FB	FB FB	FB FB	FB FB	FB FB		
36 pF	360			F			K	М	BB	BB	BB	BB		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB	İ	
39 pF	390			F			K	М	BB	ВВ	BB	ВВ		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB	1	
43 pF	430			F			K	М	ВВ	ВВ	ВВ	ВВ		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
47 pF	470			F		_	K	М	BB	BB	BB	BB		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
51 pF 56 pF	510 560			F			K	M M	BB BB	BB BB	BB BB	BB BB		CF CF	CF CF	CF CF	CF CF	CF CF	DN DN	DN DN	DN DN	DN DN	DN DN	EB EB	EB EB	EB EB	EB EB	EB EB	FB FB	FB FB	FB FB	FB FB	FB FB		
62 pF	620			F	1 -		K	М	BB	BB	BB	BB		CF	CF	CF	CF	CF	DN	DN	DN	DN		EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
68 pF	680			F	G		K	М	ВВ	ВВ	ВВ	ВВ		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
75 pF	750			F		_	K	М	ВВ	ВВ	BB	BB		CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
82 pF	820			F			K	М	BB	BB	BB	BB		CF CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB EB	EB	EB	EB	FB	FB	FB	FB	FB FB		
91 pF 100 pF	910 101			F			K	M M	BB BB	BB BB	BB BB	BB BB	ВВ	CF	CF CF	CF CF	CF CF	CF CF	DN DN	DN DN	DN DN	DN DN	DN DN	EB EB	EB	EB EB	EB EB	EB EB	FB FB	FB FB	FB FB	FB FB	FB		
110 pF	111			F			K	М	BB	BB	BB	BB	BB	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB	İ	
120 pF	121			F			K	М	ВВ	ВВ	ВВ	ВВ	ВВ	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	ЕВ	EB	EB	EB	EB	FB	FB	FB	FB	FB	İ	
130 pF	131			F	1 -	J	K	М	ВВ	ВВ	BB	ВВ	ВВ	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
150 pF	151			F	1		K	М	ВВ	ВВ	BB	BB	BB	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
160 pF	161			F	1 -		K	M	BB	BB	BB	BB	BB	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
180 pF 200 pF	181 201			F			K	M M	BB BB	BB BB	BB BB	BB BB	BB BB	CF CF	CF CF	CF CF	CF CF	CF CF	DN DN	DN DN	DN DN	DN DN	DN DN	EB EB	EB EB	EB EB	EB EB	EB EB	FB FB	FB FB	FB FB	FB FB	FB FB		
220 pF	221			F	_	_	K	М	BB	BB	BB	BB	BB	CF	CF	CF	CF	CF	DN		DN		DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
240 pF	241			F			K	М	ВВ	ВВ	ВВ	BB	ВВ	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB	İ	
270 pF	271			F		J	K	М	ВВ	ВВ	ВВ	ВВ	ВВ	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
300 pF	301			F			K	М	ВВ	ВВ	ВВ	BB	ВВ	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
330 pF	331			F		_	K	M	BB	BB	BB	BB	BB	CF	CF	CF	CF	CF	DN		DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB		
360 pF 390 pF	361 391			F	1 -		K	M M	BB BB	BB BB	BB BB	BB BB	BB BB	CF CF	CF CF	CF CF	CF CF	CF CF	DN DN	DN	DN DN	DN DN	DN DN	EB	EB EB	EB EB	EB EB	EB	FB FB	FB FB	FB FB	FB FB	FB FB		
430 pF	431			F		1	K	М	BB	BB	BB	BB	BB	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN		EB	EB	EB	EB	FB	FB	FB	FB	FB		
470 pF	471			F			K	М	BB	ВВ	ВВ	BB	BB	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN		EB	EB	EB	EB	FB	FB	FB	FB	FB	GB	GB
510 pF	511			F	G	J	K		ВВ	ВВ	ВВ	ВВ	ВВ	CF	CF	CF	CF	CF	DN	DN	DN	DN	DN		EB	EB	EB	EB	FB	FB	FB	FB	FB	GB	GB
560 pF	561			F	- 1		K		BB	ВВ	BB	BB	BB	CF	CF	CF	CF	CF	DN		DN		DN		EB	EB	EB	EB	FB	FB	FB	FB	FB	GB	GB
620 pF	621 691			F			K		BB	BB BB	BB BB	BB BB	BB	CF	CF CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB EB	EB EB	EB EB	EB	FB	FB	FB	FB	FB	GB	GB
680 pF 750 pF	681 751			F			K	M M	BB BB	BB BB	BB	BB	BB BB	CF CF	CF	CF CF	CF CF	CF CF	DN DN	DN DN	DN DN	DN DN	DN DN	EB	EB	EB	EB	EB EB	FB FB	FB FB	FB FB	FB FB	FB FB	GB GB	GB GB
820 pF	821			F			K	М	BB	BB	BB	BB	BB	CF	CF	CF	CF	CF	DN		DN		1 1	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB	GB	GB
910 pF	911			F	_		K	М	BB	ВВ	ВВ	BB	BB	CF	CF	CF	CF	CF	DN	DN	DN	DN	DP	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB	GB	GB
1,000 pF	102			F	G	J	K	М	ВВ	ВВ	ВВ	ВВ	ВВ	CF	CF	CF	CF	CF	DN	DN	DN	DN	DP	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB	GB	GB
1,100 pF	112			F					ВВ	ВВ	ВВ	BB		CF	CF	CF	CF	CF	DN		DN	DN	DP	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB	GB	GB
1,200 pF	122			F			K		BB BB	BB	BB	BB		CF	CF	CF	CF	CF CF	DN	DN	DN	DN DP	DP	EB EB	EB	EB	EB EB	EB	FB	FB	FB	FB	FB	GB	GB
1,300 pF 1,500 pF	132 152			F	_		K	M M	BB BB	BB BB	BB BB	BB BB		CF CF	CF CF	CF CF	CF CF	CF	DP DP	DP DP	DP DP	DP	DP DP	EB	EB EB	EB EB	EB	EC ED	FB FB	FB FB	FB FB	FB FB	FB FB	GB GB	GB GB
1,600 pF	162			F					00	55	00	55		CF	CF	CF	CF	CF	DP	DP	DP	DP	DP	EB	EB	EB	EB	ED	FB	FB	FB	FB	FB	GB	GB
1,800 pF	182			F			K				L		L	CF	CF	CF	CF	CF	DP	DP	DP	DP	DP	EB	EB	EB	EB		FB	FB	FB	FB	FB	GB	GB
		R	ated	l Vo	ltag			\neg	10	16	25	20	100	2	9	25	22	100	10	92	25	20	100	10	9	25	22	100	2	9	25	22	100	20	100
Capacitance	Cap		V	olta	ge (Cod	e		8	4	3	5	1	8	4	3	5	1	8	4	3	5	1	8	4	3	5	1	8	4	3	5	1	5	1
	Code	1			_						040			H	C	0603					0805					1206			t		1210		1	-	12C
	L	_`	Case Size/Series					- 101																		Щ.									

Table 1 - Capacitance Range/Selection Waterfall (0402 - 1812 Case Sizes) cont.

	Сар	Ca	se S	ize	e/S	eri	es		C)40	2C			C)60	3C			CO	80	5C			C1	120	6C			C	121	0C		C18	312C
Capacitance	Code		Volt	age	Cod	le		8	4	3	5	1	8	4	3	5	1	8	4	3	5	1	8	4	3	5	1	8	4	3	5	1	5	1
	Coue	Ra	ated V	olta	ge ((VD(C)	10	16	25	20	100	2	16	25	20	100	10	16	25	20	100	10	16	25	20	100	10	16	25	20	100	20	100
		Cap	oacita	nce	Tol	erar	ıce										duc			ility or Ch		Chi					es							,
2,000 pF	202			F	G	JΚ	М						CF	CF	CF	CF	CF	_	_	DN	_	DN	EB	EB	EB	EB		FB	FB	FB	FB	FC	GB	GB
2,200 pF	222	i I				JΚ	М						CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EE	FB	FB	FB	FB	FC	GB	GB
2,400 pF	242			F	G .	J K	M						CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EC	FB	FB	FB	FB	FC		
2,700 pF	272			F	G .	JΚ	M						CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EB	EB	EB	EB	EC	FB	FB	FB	FB	FC	GB	GB
3,000 pF	302			F	G .	J K	M						CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EC	EC	EC	EC	EC	FB	FB	FB	FB	FC		
3,300 pF	332			F	G .	J K	M						CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EC	EC	EC	EC	EE	FB	FB	FB	FB	FF	GB	GB
3,600 pF	362			F	G .	JΚ	M						CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EC	EC	EC	EC	EE	FB	FB	FB	FB	FF		
3,900 pF	392			F	G .	J K	M						CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EC	EC	EC	EC	EF	FB	FB	FB	FB	FF	GB	GB
4,300 pF	432			F	G .	JΚ	M						CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EC	EC	EC	EC	EC	FB	FB	FB	FB	FF	ĺ	
4,700 pF	472			F	G L	JΚ	M						CF	CF	CF	CF	CF	DN	DN	DN	DN	DN	EC	EC	EC	EC	EC	FF	FF	FF	FF	FG	GB	GB
5,100 pF	512			F	G L	JΚ	M						CF	CF	CF	CF		DN	DN	DN	DN	DN	ED	ED	ED	ED	ED	FB	FB	FB	FB	FG	1	
5,600 pF	562			F	G .								CF	CF	CF	CF		DN	DN	DN	DN	DN	ED	ED	ED	ED	ED	FB	FB	FB	FB	FG	GB	GB
6,200 pF	622			F (G	J K	M						CF	CF	CF	CF		DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FG		
6,800 pF	682			F	G L	ΙK	M						CF	CF	CF	CF		DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FB	FB	FB	FB	FG	GB	GB
7,500 pF	752			F	G .	ΙK	M						CF	CF	CF			DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FC	FC	FC	FC	FC		
8,200 pF	822			F	G .	JΚ	M						CF	CF	CF			DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FC	FC	FC	FC	FC	GB	GH
9,100 pF	912			F	G .	JΚ	M						CF	CF	CF			DN	DN	DN	DN	DN	EB	EB	EB	EB	EB	FE	FE	FE	FE	FE		
10,000 pF	103			F	G .	JΚ	M						CF	CF	CF			DN	DN	DN	DN	DP	EB	EB	EB	EB	EB	FF	FF	FF	FF	FF	GB	GH
12,000 pF	123			F	G .	JΚ	M						İ					DN	DN	DN	DN	DE	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB	GB	GG
15,000 pF	153			F	G .	JΚ	M						İ					DN	DN	DN	DP	DG	EB	EB	EB	EB	EB	FB	FB	FB	FB	FB	GB	GB
18,000 pF	183			F	G .	JΚ	M						l					DN	DN	DN	DP		EB	EB	EB	EB	EB	FB	FB	FB	FB	FB	GB	GB
22,000 pF	223			F	G .	JΚ	M						İ					DP	DP	DP	DF		EB	EB	EB	EB	EC	FB	FB	FB	FB	FB	GB	GB
27,000 pF	273			F	G	J K	M						İ					DF	DF	DF			EB	EB	EB	EB	EE	FB	FB	FB	FB	FB	GB	GB
33,000 pF	333			F	G .	JΚ	M						İ					DG	DG	DG			EB	EB	EB	EB	EE	FB	FB	FB	FB	FB	GB	GB
39,000 pF	393			F	G .	JΚ	M						l										EC	EC	EC	EE	EH	FB	FB	FB	FB	FE	GB	GB
47,000 pF	473			F	G .	JΚ	M						İ					Ī					EC	EC	EC	EE	EH	FB	FB	FB	FB	FE	GB	GB
56,000 pF	563			F	G .	JΚ	M						İ					Ī					ED	ED	ED	EF		FB	FB	FB	FB	FF	GB	GB
68,000 pF	683			F (G .	JΚ	М																EF	EF	EF	EH		FB	FB	FB	FC	FG	GB	GB
82,000 pF	823			F	G .	JΚ	М						I										EH	EH	EH	EH		FC	FC	FC	FF	FH	GB	GB
100,000 pF	104			F	G .	JΚ	М						l					Ī					EH	EH	EH			FE	FE	FE	FG	FM	GB	GD
120,000 pF	124			F	G .	JΚ	М						l					Ī					İ					FG	FG	FG	FH		GB	GH
150,000 pF	154			F	G .	JΚ	М						l					Ī					İ					FH	FH	FH	FM		GD	GN
180,000 pF	184			F	G .	J K	M																					FJ	FJ	FJ			GH	
220,000 pF	224			F (G .	J K	М																L										GK	
		Ra	ited V	olta	ge ((VD	C)	10	16	25	20	100	10	16	25	20	100	10	16	25	20	100	10	16	25	20	100	10	16	25	20	100	20	100
Capacitance	Cap Code		Vol	age	Cod	le		8	4	3	5	1	8	4	3	5	1	8	4	3	5	1	8	4	3	5	1	8	4	3	5	1	5	1
	5540	С	Voltage Code Case Size/Series				С	040	2C			C	0603	3C			C	0805	5C			С	1206	6C			C	121	ОС		C18	312C		



Table 2A - Chip Thickness/Tape & Reel Packaging Quantities

Thickness	Case	Thickness ±	Paper C	Quantity	Plastic (Quantity
Code	Size ¹	Range (mm)	7" Reel	13" Reel	7" Reel	13" Reel
BB	0402	0.50 ±0.05	10,000	50,000	0	0
CF	0603	0.80 ±0.07*	4,000	15,000	0	0
DN	0805	0.78 ±0.10*	4,000	15,000	0	0
DP	0805	0.90 ±0.10*	4,000	15,000	0	0
DE	0805	1.00 ±0.10	0	0	2,500	10,000
DF	0805	1.10 ±0.10	0	0	2,500	10,000
DG	0805	1.25 ±0.15	0	0	2,500	10,000
EB	1206	0.78 ±0.10	0	0	4,000	10,000
EC	1206	0.90 ±0.10	0	0	4,000	10,000
ED	1206	1.00 ±0.10	0	0	2,500	10,000
EE	1206	1.10 ±0.10	0	0	2,500	10,000
EF	1206	1.20 ±0.15	0	0	2,500	10,000
EH	1206	1.60 ±0.20	0	0	2,000	8,000
FB	1210	0.78 ±0.10	0	0	4,000	10,000
FC	1210	0.90 ±0.10	0	0	4,000	10,000
FE	1210	1.00 ±0.10	0	0	2,500	10,000
FF	1210	1.10 ±0.10	0	0	2,500	10,000
FG	1210	1.25 ±0.15	0	0	2,500	10,000
FH	1210	1.55 ±0.15	0	0	2,000	8,000
FM	1210	1.70 ±0.20	0	0	2,000	8,000
FJ	1210	1.85 ±0.20	0	0	2,000	8,000
GB	1812	1.00 ±0.10	0	0	1,000	4,000
GD	1812	1.25 ±0.15	0	0	1,000	4,000
GH	1812	1.40 ±0.15	0	0	1,000	4,000
GG	1812	1.55 ±0.10	0	0	1,000	4,000
GK	1812	1.60 ±0.20	0	0	1,000	4,000
GN	1812	1.70 ±0.20	0	0	1,000	4,000
Thickness	Case	Thickness ±	7" Reel	13" Reel	7" Reel	13" Reel
Code	Size ¹	Range (mm)	Paper Q	uantity ¹	Plastic (Quantity

Package quantity based on finished chip thickness specifications.

Table 2B - Bulk Packaging Quantities

Dookogi	ing Type	Loose Pa	ackaging
Packagi	ing Type	Bulk Bag	(default)
Packagin	g C-Spec ¹	N/	'A²
Case	Size	Packaging Quantities (pieces/unit packaging)
EIA (in)	Metric (mm)	Minimum	Maximum
0402	1005		
0603	1608		
0805	2012		50,000
1206	3216		
1210	3225	1	
1808	4520	1	
1812	4532		
1825	4564		20,000
2220	5650		
2225	5664		

¹ The "Packaging C-Spec" is a 4 to 8 digit code which identifies the packaging type and/or product grade. When ordering, the proper code must be included in the 15th through 22nd character positions of the ordering code. See "Ordering Information" section of this document for further details. Commercial Grade product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging. Contact KEMET if you require a bulk bag packaging option for Automotive Grade products.

² A packaging C-Spec (see note 1 above) is not required for "Bulk Bag" packaging (excluding Anti-Static Bulk Bag and Automotive Grade products). The 15th through 22nd character positions of the ordering code should be left blank. All product ordered without a packaging C-Spec will default to our standard "Bulk Bag" packaging.

Table 3 - Chip Capacitor Land Pattern Design Recommendations per IPC-7351


EIA Size Code	Metric Size Code		Maxi	sity Lev mum (N rotrusio	Most))		Media	sity Lev an (Nor rotrusio)		Mini	sity Lev mum (L rotrusio		ı)
Jouc	oouc	С	Y	X	V 1	V2	С	Y	X	V1	V2	С	Y	X	V1	V2
0402	1005	0.50	0.72	0.72	2.20	1.20	0.45	0.62	0.62	1.90	1.00	0.40	0.52	0.52	1.60	0.80
0603	1608	0.90	1.15	1.10	4.00	2.10	0.80	0.95	1.00	3.10	1.50	0.60	0.75	0.90	2.40	1.20
0805	2012	1.00	1.35	1.55	4.40	2.60	0.90	1.15	1.45	3.50	2.00	0.75	0.95	1.35	2.80	1.70
1206	3216	1.60	1.35	1.90	5.60	2.90	1.50	1.15	1.80	4.70	2.30	1.40	0.95	1.70	4.00	2.00
1210	3225	1.60	1.35	2.80	5.65	3.80	1.50	1.15	2.70	4.70	3.20	1.40	0.95	2.60	4.00	2.90
1210¹	3225	1.50	1.60	2.90	5.60	3.90	1.40	1.40	2.80	4.70	3.30	1.30	1.20	2.70	4.00	3.00
1812	4532	2.15	1.60	3.60	6.90	4.60	2.05	1.40	3.50	6.00	4.00	1.95	1.20	3.40	5.30	3.70

¹ Only for capacitance values ≥ 22 μF.

Density Level A: For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes. KEMET only recommends wave soldering of EIA 0603, 0805 and 1206 case sizes.

Density Level B: For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes. **Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC Standard 7351 (IPC-7351).

Image below based on Density Level B for an EIA 1210 case size.



Soldering Process

Recommended Soldering Technique:

- Solder wave or solder reflow for EIA case sizes 0603, 0805 and 1206
- · All other EIA case sizes are limited to solder reflow only

Recommended Reflow Soldering Profile:

KEMET's families of surface mount multilayer ceramic capacitors (SMD MLCCs) are compatible with wave (single or dual), convection, IR or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/J-STD-020 standard for moisture sensitivity testing. These devices can safely withstand a maximum of three reflow passes at these conditions.

Profile Feature	Termination Finish			
1 Tome Teature	SnPb	100% Matte Sn		
Preheat/Soak				
Temperature Minimum (T _{Smin})	100°C	150°C		
Temperature Maximum (T _{Smax})	150°C	200°C		
Time (t_s) from T_{Smin} to T_{Smax}	60 - 120 seconds	60 - 120 seconds		
Ramp-Up Rate (T _L to T _p)	3°C/second maximum	3°C/second maximum		
Liquidous Temperature (T _L)	183°C	217°C		
Time Above Liquidous (t _L)	60 - 150 seconds	60 - 150 seconds		
Peak Temperature (T _P)	235°C	260°C		
Time Within 5°C of Maximum Peak Temperature (t _p)	20 seconds maximum	30 seconds maximum		
Ramp-Down Rate (T _p to T _L)	6°C/second maximum	6°C/second maximum		
Time 25°C to Peak Temperature	6 minutes maximum	8 minutes maximum		

Note 1: All temperatures refer to the center of the package, measured on the capacitor body surface that is facing up during assembly reflow.





Table 4 - Performance & Reliability: Test Methods & Conditions

Stress	Reference	Test or Inspection Method
Terminal Strength	JIS-C-6429	Appendix 1, Note: Force of 1.8 kg for 60 seconds.
Board Flex	JIS-C-6429	Appendix 2, Note: Standard termination system – 2.0 mm (minimum) for all except 3 mm for COG. Flexible termination system – 3.0 mm (minimum).
		Magnification 50 X. Conditions:
Solderability	J-STD-002	a) Method B, 4 hours at 155°C, dry heat at 235°C
Solderability	J-31D-002	b) Method B at 215°C category 3
		c) Method D, category 3 at 260°C
Temperature Cycling	JESD22 Method JA-104	1,000 cycles (-55°C to +150°C). Measurement at 24 hours ±4 hours after test conclusion.
Biased Humidity MIL-STD-202 Method		Load Humidity: 1,000 hours 85°C/85%RH and rated voltage. Add 100K ohm resistor. Measurement at 24 hours ±4 hours after test conclusion.
Bracea Frankaity	103	Low Volt Humidity: 1,000 hours 85°C/85% RH and 1.5 V. Add 100 K ohm resistor. Measurement at 24 hours ±4 hours after test conclusion.
Moisture Resistance	MIL-STD-202 Method 106	t = 24 hours/cycle. Steps 7a and 7b not required. Measurement at 24 hours. ±4 hours after test conclusion.
Thermal Shock	MIL-STD-202 Method 107	-55°C/+150. Note: Number of cycles required – 300. Maximum transfer time – 20 seconds. Dwell time – 15 minutes. Air – Air.
High Temperature Life	MIL-STD-202 Method 108 /EIA-198	1,000 hours at 150°C with 2 X rated voltage applied.
Storage Life	MIL-STD-202 Method 108	150°C, 0 VDC for 1,000 hours.
Vibration	MIL-STD-202 Method 204	5 g's for 20 min., 12 cycles each of 3 orientations. Note: Use 8" X 5" PCB 0.031" thick 7 secure points on one long side and 2 secure points at corners of opposite sides. Parts mounted within 2" from any secure point. Test from 10 – 2,000 Hz.
Mechanical Shock	MIL-STD-202 Method 213	Figure 1 of Method 213, Condition F.
Resistance to Solvents	MIL-STD-202 Method 215	Add aqueous wash chemical, OKEM Clean or equivalent.

Storage and Handling

Ceramic chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature – reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 70% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulfur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within 1.5 years of receipt.

Construction



Capacitor Marking (Optional)

Laser marking option is not available on:

- COG, Ultra Stable X8R and Y5V dielectric devices.
- · EIA 0402 case size devices.
- EIA 0603 case size devices with Flexible Termination option.
- · KPS Commercial and Automotive grade stacked devices.

These capacitors are supplied unmarked only.



Tape & Reel Packaging Information

KEMET offers multilayer ceramic chip capacitors packaged in 8, 12 and 16 mm tape on 7" and 13" reels in accordance with EIA Standard 481. This packaging system is compatible with all tape-fed automatic pick and place systems. See Table 2 for details on reeling quantities for commercial chips.




Table 5 - Carrier Tape Configuration, Embossed Plastic & Punched Paper (mm)

EIA Case Size	Tape Size (W)*	Embosse	ed Plastic	Punched Paper		
		7" Reel	13" Reel	7" Reel	13" Reel	
		Pitch (P ₁)*		Pitch (P ₁)*		
01005 - 0402	8			2	2	
0603	8			4	4	
0805	8	4	4	4	4	
1206 - 1210	8	4	4	4	4	
1805 – 1808	12	4	4			
≥ 1812	12	8	8			
KPS 1210	12	8	8			
KPS 1812 and 2220	16	12	12			
Array 0612	8	4	4			

^{*}Refer to Figures 1 and 2 for W and P_1 carrier tape reference locations.



^{*}Refer to Tables 6 and 7 for tolerance specifications.

Figure 1 – Embossed (Plastic) Carrier Tape Dimensions




Table 6 – Embossed (Plastic) Carrier Tape Dimensions

Metric will govern

Constant Dimensions — Millimeters (Inches)									
Tape Size	D ₀	D ₁ Minimum Note 1	E ₁	P ₀	P ₂	R Reference Note 2	S ₁ Minimum Note 3	T Maximum	T ₁ Maximum
8 mm		1.0 (0.039)				25.0 (0.984)			
12 mm	1.5 +0.10/-0.0 (0.059 +0.004/-0.0)	1.0	1.75 ±0.10 (0.069 ±0.004)	4.0 ±0.10 (0.157 ±0.004)	2.0 ±0.05 (0.079 ±0.002)	30	0.600 (0.024)	0.600 (0.024)	0.100 (0.004)
16 mm		(0.059)	(0.059)			(1.181)			
Variable Dimensions — Millimeters (Inches)									
		1	Variable Dime	ensions — Mil	limeters (Inch	ies)			
Tape Size	Pitch	B ₁ Maximum Note 4	Variable Dime E ₂ Minimum	ensions — Mill F	P ₁	T ₂ Maximum	W Maximum	A ₀ ,B ₀	& K ₀
Tape Size	Pitch Single (4 mm)	B ₁ Maximum	E ₂		,	T ₂		A ₀ ,B ₀	& K ₀
•		B ₁ Maximum Note 4 4.35	E ₂ Minimum 6.25	F 3.5 ±0.05	P ₁ 4.0 ±0.10	T ₂ Maximum 2.5	Maximum 8.3	· ·	& K ₀

- 1. The embossment hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of the embossment location and the hole location shall be applied independently of each other.
- 2. The tape with or without components shall pass around R without damage (see Figure 6.)
- 3. If $S_1 < 1.0$ mm, there may not be enough area for a cover tape to be properly applied (see EIA Standard 481, paragraph 4.3, section b.)
- 4. B, dimension is a reference dimension for tape feeder clearance only.
- 5. The cavity defined by A_{n} , B_{n} and K_{n} shall surround the component with sufficient clearance that:
 - (a) the component does not protrude above the top surface of the carrier tape.
 - (b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.
 - (c) rotation of the component is limited to 20° maximum for 8 and 12 mm tapes and 10° maximum for 16 mm tapes (see Figure 3.)
 - (d) lateral movement of the component is restricted to 0.5 mm maximum for 8 and 12 mm wide tape and to 1.0 mm maximum for 16 mm tape (see Figure 4.)
 - (e) for KPS product, A_a and B_a are measured on a plane 0.3 mm above the bottom of the pocket.
 - (f) see addendum in EIA Standard 481 for standards relating to more precise taping requirements.



Figure 2 - Punched (Paper) Carrier Tape Dimensions




Table 7 - Punched (Paper) Carrier Tape Dimensions

Metric will govern

Constant Dimensions — Millimeters (Inches)								
Tape Size	D ₀	E ₁	P ₀	P ₂	T ₁ Maximum	G Minimum	R Reference Note 2	
8 mm	1.5 +0.10 -0.0 (0.059 +0.004 -0.0)	1.75 ±0.10 (0.069 ±0.004)	4.0 ±0.10 (0.157 ±0.004)	2.0 ±0.05 (0.079 ±0.002)	0.10 (0.004) maximum	0.75 (0.030)	25 (0.984)	
	Variable Dimensions — Millimeters (Inches)							
Tape Size	Pitch	E2 Minimum	F	P ₁	T Maximum	W Maximum	A_0B_0	
8 mm	Single (4 mm)	6.25 (0.246)	3.5 ±0.05 (0.138 ±0.002)	4.0 ±0.10 (0.157 ±0.004)	1.1 (0.043)	8.3 (0.327)	Note 1	

- 1. The cavity defined by A_{α} B_{α} and T shall surround the component with sufficient clearance that:
 - a) the component does not protrude beyond either surface of the carrier tape.
 - b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.
 - c) rotation of the component is limited to 20° maximum (see Figure 3.)
 - d) lateral movement of the component is restricted to 0.5 mm maximum (see Figure 4.)
 - e) see addendum in EIA Standard 481 for standards relating to more precise taping requirements.
- 2. The tape with or without components shall pass around R without damage (see Figure 6.)



Packaging Information Performance Notes


- 1. Cover Tape Break Force: 1.0 kg minimum.
- 2. Cover Tape Peel Strength: The total peel strength of the cover tape from the carrier tape shall be:

Tape Width	Peel Strength		
8 mm	0.1 to 1.0 newton (10 to 100 gf)		
12 and 16 mm	0.1 to 1.3 newton (10 to 130 gf)		

The direction of the pull shall be opposite the direction of the carrier tape travel. The pull angle of the carrier tape shall be 165° to 180° from the plane of the carrier tape. During peeling, the carrier and/or cover tape shall be pulled at a velocity of 300 ±10 mm/minute.

3. Labeling: Bar code labeling (standard or custom) shall be on the side of the reel opposite the sprocket holes. *Refer to EIA Standards 556 and 624*.

Figure 3 - Maximum Component Rotation






Figure 4 – Maximum Lateral Movement




Figure 5 - Bending Radius





Figure 6 - Reel Dimensions



Note: Drive spokes optional; if used, dimensions B and D shall apply.

Table 8 - Reel Dimensions

Metric will govern

Constant Dimensions — Millimeters (Inches)							
Tape Size	A	B Minimum	С	D Minimum			
8 mm	178 ±0.20						
12 mm	(7.008 ±0.008) or	1.5 (0.059)	13.0 +0.5/-0.2 (0.521 +0.02/-0.008)	20.2 (0.795)			
16 mm	330 ±0.20 (13.000 ±0.008)	, ,	,	(*** : *)			
	Variable Dimensions — Millimeters (Inches)						
Tape Size	N Minimum	W ₁	W ₂ Maximum	W ₃			
8 mm		8.4 +1.5/-0.0 (0.331 +0.059/-0.0)	14.4 (0.567)				
12 mm	50 (1.969)	12.4 +2.0/-0.0 (0.488 +0.078/-0.0)	18.4 (0.724)	Shall accommodate tape width without interference			
16 mm		16.4 +2.0/-0.0 (0.646 +0.078/-0.0)	22.4 (0.882)				

Figure 7 - Tape Leader & Trailer Dimensions





Figure 8 - Maximum Camber





High Temperature 150°C, Ultra-Stable X8R Dielectric, 10 - 100 VDC (Commercial & Automotive Grade)

Surface Mount Multilayer Ceramic Chip Capacitors (SMD MLCCs)

KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without quarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute - and KEMET specifically disclaims - any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

